



WXP0023

**Plate gallery plastic 3 gang vertical 57mm pure-white**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Dimensions**

Depth 9.3 mm

Height 202 mm

Width 92 mm

**Capacity**

Number of sockets 3

**Materials**

Free area for finishing name pure

Colour white

Surface appearance glossy

Type of surface treatment untreated

**Installation, mounting**

Mounting way vertical

**Standards**

European directive WEEE not concerned

**Safety**

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Use conditions**

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

**Identification**

Range gallery

Composition Surface mounted frame