



WXP0096

Plate gallery plastic 1K 8 modules + 8 modules pure-white

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Number of modules	16
-------------------	----

Dimensions

Depth	9.3 mm
-------	--------

Height	164 mm
--------	--------

Width	235 mm
-------	--------

Capacity

Number of sockets	2
-------------------	---

Materials

Free area for finishing name	pure
------------------------------	------

Colour	white
--------	-------

Surface appearance	glossy
--------------------	--------

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Mounting way	horizontal
--------------	------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
---	----

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

Identification

Range	gallery
-------	---------

Composition	Surface mounted frame
-------------	-----------------------