


WXP0202



## Plate gallery plastic plastic 1 gang night

### Technical properties

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Dimensions

Depth	9.3 mm
Height	88 mm
Width	92 mm

#### Capacity

Number of sockets	1
-------------------	---

#### Materials

Free area for finishing name	night
Surface appearance	mat

#### Installation, mounting

Mounting way	horizontal
--------------	------------

#### Equipment

With transparent product label holder	No
---------------------------------------	----

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

#### Identification

Range	gallery
Composition	Surface mounted frame