



WXP0223

## Plate gallery plastic plastic 3 gang vertical 57mm night

### Technical properties

#### Architecture

Fixing mode Clipped

#### Dimensions

Depth 9.3 mm

Height 202 mm

Width 92 mm

#### Capacity

Number of sockets 3

#### Materials

Free area for finishing name night

Surface appearance matt

#### Installation, mounting

Mounting way vertical

#### Equipment

With transparent product label holder No

#### Standards

European directive WEEE not concerned

#### Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Range gallery

Composition Surface mounted frame