



WXP0304

Plate gallery plastic plastic 4 modules enteraxe 71mm dune

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 9.3 mm

Height 88 mm

Width 163 mm

Capacity

Number of sockets 1

Materials

Free area for finishing name dune

RAL colour RAL 1013 - Oyster white

Type of surface treatment untreated

Installation, mounting

Mounting way horizontal

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Surface mounted frame