



WXP0342

Plate gallery plastic plastic 2 gang vertical 71mm dune

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 9.3 mm

Height 159 mm

Width 92 mm

Capacity

Number of sockets 2

Materials

Free area for finishing name dune

Colour dune

RAL colour RAL 1013 - Oyster white

Material Polycarbonate (PC)

Surface appearance glossy

Type of surface treatment untreated

Installation, mounting

Mounting way vertical

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Protection index IP IP21

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

