



WXP0408

Plate gallery plastic plastic 8 modules enteraxe 71mm champagne

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 9.3 mm

Height 88 mm

Width 235 mm

Capacity

Number of sockets 1

Materials

Free area for finishing name champagne

RAL colour RAL 1036 - Pearl gold

Surface appearance matt

Type of surface treatment Painted

Installation, mounting

Mounting way horizontal

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Surface mounted frame