



WXP0412

Plate gallery plastic plastic 2 gang horizontal 71mm champagne

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	9.3 mm
Height	88 mm
Width	163 mm

Capacity

Number of sockets	2
-------------------	---

Materials

Free area for finishing name	champagne
RAL colour	RAL 1036 - Pearl gold
Material	Polycarbonate (PC)
Surface appearance	matt
Type of surface treatment	Painted

Installation, mounting

Mounting way	horizontal
--------------	------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP21
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C