



WXP0643

Plate gallery plastic plastic 3 gang vertical 71mm eglantine

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	9.3 mm
Height	230 mm
Width	92 mm

Capacity

Number of sockets	3
-------------------	---

Materials

Free area for finishing name	eglantine
RAL colour	RAL 3012 - Beige red
Material	Polycarbonate (PC)
Surface appearance	matt
Type of surface treatment	Painted

Installation, mounting

Mounting way	vertical
--------------	----------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP21
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C