



WXP0704

Plate gallery plastic plastic 4 modules enteraxe 71mm river

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 9.3 mm

Height 88 mm

Width 163 mm

Capacity

Number of sockets 1

Materials

Free area for finishing name river

Colour blue (shades)

RAL colour RAL 5025 - Pearl gentian blue

Material Polycarbonate (PC)

Surface appearance matt

Type of surface treatment Painted

Installation, mounting

Mounting way horizontal

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Protection index IP IP21

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Surface mounted frame