



WXP2006

Plate gallery 6 modules enteraxe 57mm aluminium leaf

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 9.3 mm

Height 88 mm

Width 206 mm

Capacity

Number of sockets 1

Materials

Free area for finishing name aluminium

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Surface appearance matt

Type of surface treatment brushed

Installation, mounting

Mounting way horizontal

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Surface mounted frame