



WXP2106

## Plate gallery 6 modules enteraxe 57mm steel leaf

### Technical properties

#### Architecture

Fixing mode Clipped

#### Dimensions

Depth 9.3 mm

Height 88 mm

Width 206 mm

#### Capacity

Number of sockets 1

#### Materials

Free area for finishing name steel

Colour stainless steel optics

RAL colour RAL 7048 - Pearl mouse grey

Material Plastic/metal

Surface appearance matt

Type of surface treatment brushed

#### Installation, mounting

Mounting way horizontal

#### Equipment

With transparent product label holder No

#### Standards

European directive WEEE not concerned

#### Safety

IK protection code against mechanical impacts 05

Protection index IP IP21

RoHS conform Yes

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Range gallery

Composition Surface mounted frame