



WXP2134

**Plate gallery 4 modules enteraxe 57mm steel leaf**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Dimensions**

Depth 9.3 mm

Height 88 mm

Width 149 mm

**Capacity**

Number of sockets 1

**Materials**

Free area for finishing name steel

Surface appearance matt

**Installation, mounting**

Mounting way horizontal

**Equipment**

With transparent product label holder No

**Standards**

European directive WEEE not concerned

**Safety**

IK protection code against mechanical impacts 05

RoHS conform Yes

**Use conditions**

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

**Identification**

Range gallery

Composition Surface mounted frame