



WXP2222

**Plate gallery 2 gang vertical 57mm bronze leaf**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Dimensions**

Depth	9.3 mm
Height	145 mm
Width	92 mm

**Capacity**

Number of sockets	2
-------------------	---

**Materials**

Free area for finishing name	bronze
RAL colour	RAL 3012 - Beige red
Material	Plastic/metal
Surface appearance	matt
Type of surface treatment	brushed

**Installation, mounting**

Mounting way	vertical
--------------	----------

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

IK protection code against mechanical impacts	05
RoHS conform	Yes

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

**Identification**

Composition	Surface mounted frame
-------------	-----------------------