



WXP2406

Plate gallery 6 modules enteraxe 57mm pecan

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	9.3 mm
Height	88 mm
Width	206 mm

Capacity

Number of sockets	1
-------------------	---

Materials

Free area for finishing name	pecan
Surface appearance	matt

Installation, mounting

Mounting way	horizontal
--------------	------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
RoHS conform	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	Surface mounted frame