



WXP2414

## Plate gallery 4 gang horizontal 71mm pecan

### Technical properties

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Dimensions

Depth	9.3 mm
Height	88 mm
Width	305 mm

#### Capacity

Number of sockets	4
-------------------	---

#### Materials

Free area for finishing name	pecan
Surface appearance	matt

#### Installation, mounting

Mounting way	horizontal
--------------	------------

#### Equipment

With transparent product label holder	No
---------------------------------------	----

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

IK protection code against mechanical impacts	05
RoHS conform	Yes

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

#### Identification

Composition	Surface mounted frame
-------------	-----------------------