



WXP2443

Plate gallery 3 gang vertical 71mm pecan

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 9.3 mm

Height 230 mm

Width 92 mm

Capacity

Number of sockets 3

Materials

Free area for finishing name pecan

Colour dark wood optics

RAL colour RAL 8025 - Pale brown

Material wood

Surface appearance matt

Type of surface treatment Untreated

Installation, mounting

Mounting way vertical

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Protection index IP IP21

RoHS conform Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Surface mounted frame