



WXP2542

Plate gallery 2 gang vertical 71 mm latté

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	9.3 mm
Height	159 mm
Width	92 mm

Capacity

Number of sockets	2
-------------------	---

Materials

Free area for finishing name	latté
Surface appearance	mat

Installation, mounting

Mounting way	vertical
--------------	----------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
RoHS conform	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Composition	Surface mounted frame
-------------	-----------------------