



WXP4006

Plate gallery 6 modules enteraxe 57mm moon glass material

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	9.3 mm
-------	--------

Height	87.7 mm
--------	---------

Width	206 mm
-------	--------

Capacity

Number of sockets	1
-------------------	---

Materials

Free area for finishing name	moon glass
------------------------------	------------

Colour	white
--------	-------

Material	glass
----------	-------

Surface appearance	matt
--------------------	------

Installation, mounting

Mounting way	horizontal
--------------	------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
---	----

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

Identification

Range	gallery
-------	---------

Composition	Surface mounted frame
-------------	-----------------------