



WXP4013

**Plate gallery 3 gang horizontal 71mm moon glass material**

**Technical properties**

**Architecture**

|             |         |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

**Dimensions**

|        |         |
|--------|---------|
| Depth  | 9.3 mm  |
| Height | 87.7 mm |
| Width  | 234 mm  |

**Capacity**

|                   |   |
|-------------------|---|
| Number of sockets | 3 |
|-------------------|---|

**Materials**

|                           |       |
|---------------------------|-------|
| Colour                    | white |
| Material                  | glass |
| Surface appearance        | matt  |
| Type of surface treatment | Other |

**Installation, mounting**

|              |            |
|--------------|------------|
| Mounting way | horizontal |
|--------------|------------|

**Equipment**

|                                       |    |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

**Standards**

|                         |               |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

**Safety**

|                                               |      |
|-----------------------------------------------|------|
| IK protection code against mechanical impacts | 05   |
| Protection index IP                           | IP21 |
| REACH conform                                 | Yes  |
| RoHS conform                                  | Yes  |

**Use conditions**

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -10...35 °C |
| Storage/transport temperature | -10...50 °C |