



WXP4042

Plate gallery 2 gang vertical 71mm moon glass material

Technical properties

Architecture

| | |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

Dimensions

| | |
|--------|----------|
| Depth | 9.3 mm |
| Height | 158.7 mm |
| Width | 92 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 2 |
|-------------------|---|

Materials

| | |
|------------------------------|------------|
| Free area for finishing name | moon glass |
| Colour | white |
| Material | glass |
| Surface appearance | matt |
| Type of surface treatment | Other |

Installation, mounting

| | |
|--------------|----------|
| Mounting way | vertical |
|--------------|----------|

Equipment

| | |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|---|-----|
| IK protection code against mechanical impacts | 05 |
| REACH conform | Yes |
| RoHS conform | Yes |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

Identification

| | |
|-------------|-----------------------|
| Composition | Surface mounted frame |
|-------------|-----------------------|