



WXP4208

Plate gallery 8 modules enteraxe 71mm bright inox material

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	9.3 mm
-------	--------

Height	87.7 mm
--------	---------

Width	235 mm
-------	--------

Capacity

Number of sockets	1
-------------------	---

Materials

Free area for finishing name	bright inox
------------------------------	-------------

Colour	stainless steel optics
--------	------------------------

RAL colour	RAL 9007 - Grey aluminium
------------	---------------------------

Material	stainless steel
----------	-----------------

Surface appearance	matt
--------------------	------

Type of surface treatment	brushed
---------------------------	---------

Installation, mounting

Mounting way	horizontal
--------------	------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
---	----

Protection index IP	IP21
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

Identification

Range	gallery
-------	---------

