



WXP4208

**Plate gallery 8 modules enteraxe 71mm bright inox material**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Dimensions**

Depth	9.3 mm
Height	87.7 mm
Width	235 mm

**Capacity**

Number of sockets	1
-------------------	---

**Materials**

Free area for finishing name	bright inox
Colour	stainless steel optics
Material	stainless steel
Surface appearance	matt
Type of surface treatment	brushed

**Installation, mounting**

Mounting way	horizontal
--------------	------------

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

IK protection code against mechanical impacts	05
Protection index IP	IP21
REACH conform	Yes
RoHS conform	Yes

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C