

Surface mounted frame



WXP4802

## Plate gallery 1 gang grey wood material

## **Technical properties**

Architecture	
Fixing mode	Clipped
Dimensions	
Depth	9.3 mm
Height	87.7 mm
Width	92 mm
Capacity	
Number of sockets	1
Materials	
Free area for finishing name	grey wood
Surface appearance	matt
Installation, mounting	
Mounting way	horizontal
Standards	
European directive WEEE	not concerned
Safety	
IK protection code against mecanical impacts	05
RoHS conform	Yes
Use conditions	
Operating temperature	-1035 °C
Storage/transport temperature	-1050 °C
Identification	
Range	gallery

Composition