



WXP4808

Plate gallery 8 modules enteraxe 71mm grey wood material

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 9.3 mm

Height 87.7 mm

Width 235 mm

Capacity

Number of sockets 1

Materials

Free area for finishing name grey wood

Colour dark wood optics

RAL colour RAL 7006 - Beige grey

Material wood

Surface appearance matt

Type of surface treatment Plating

Installation, mounting

Mounting way horizontal

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Protection index IP IP21

RoHS conform Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Surface mounted frame