



WXP5004

Plate gallery 4 modules enteraxe 71mm mirror glass material

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	9.3 mm
-------	--------

Height	87.7 mm
--------	---------

Width	163 mm
-------	--------

Capacity

Number of sockets	1
-------------------	---

Materials

Free area for finishing name	mirror glass
------------------------------	--------------

Surface appearance	glossy
--------------------	--------

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Mounting way	horizontal
--------------	------------

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
---	----

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

Identification

Range	gallery
-------	---------

Composition	Surface mounted frame
-------------	-----------------------