



WXP5014

Plate gallery 4 gang horizontal 71mm mirror glass material

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	9.3 mm
Height	87.7 mm
Width	305 mm

Capacity

Number of sockets	4
-------------------	---

Materials

Free area for finishing name	mirror glass
Colour	silver optics
Material	glass
Type of surface treatment	untreated

Installation, mounting

Mounting way	horizontal
--------------	------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP21
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C