



WXP9902

Plate gallery plastic 1 gang antibacterial

Technical properties

Architecture

| | |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

Dimensions

| | |
|--------|--------|
| Depth | 9.3 mm |
| Height | 88 mm |
| Width | 92 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

Materials

| | |
|------------------------------|---------------|
| Free area for finishing name | antibactérien |
| Colour | white |
| Surface appearance | glossy |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|--------------|------------|
| Mounting way | horizontal |
|--------------|------------|

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|---|-----|
| IK protection code against mechanical impacts | 05 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

Identification

| | |
|-------------|-----------------------|
| Range | gallery |
| Composition | Surface mounted frame |