



WXP9912

Plate gallery plastic 2 gang horizontal 71mm antibacterial

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 9.3 mm

Height 88 mm

Width 163 mm

Capacity

Number of sockets 2

Materials

Free area for finishing name antibactérien

Colour white

Type of surface treatment untreated

Installation, mounting

Mounting way horizontal

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Surface mounted frame