



XEV103

EV charging station witty home 1x22kW 3P M3T2S M2TE IP54

Technical properties

Architecture

Connection system	Typ 2
-------------------	-------

Functions

Function access control	No
With load management	Yes

Connectivity

Number of charging points	1
Number of CEE socket outlets	0
Number of socket outlets GB	0
Number of socket outlets Type 2	1
Number of socket outlets Type 3	0
Number of vehicle connectors CHAdeMO	0
Number of vehicle connectors Type 1	0
Number of vehicle connectors Type 1 CCS	0
Number of vehicle connectors Type 2	0
Number of vehicle connectors Type 2 CCS	0

Main electrical features

Nominal voltage	230/400 V
Frequency	50 Hz
Rated current	32 A

Dimensions

Depth of installed product	233 mm
Height of installed product	480 mm
Length	480 mm
Width of installed product	346 mm

Power

connected load	22 kW
Max. power per charging point	22 kW

Power supply

Number of phases for the power supply	3 phases
---------------------------------------	----------

Materials

RAL colour	RAL 7035 - Light grey
Material	plastic

Material group other

Equipment

With energy meter	No
With house connection box	No
Number of household socket outlets	1
Number of vehicle connectors GB AC	0
Number of vehicle connectors GB DC	0
With circuit breaker	No

Standards

European directive RoHs	compliant
-------------------------	-----------

Safety

Protection index IP	IP54
REACH conform	No
Halogen free	No
Impact strength	IK10