



XEV103

**EV charging station witty home 1x22kW 3P M3T2S M2TE IP54**

**Technical properties**

**Architecture**

Connection system	Typ 2
-------------------	-------

**Functions**

Function access control	No
With load management	Yes

**Connectivity**

Number of charging points	1
Number of CEE socket outlets	0
Number of socket outlets GB	0
Number of socket outlets Type 2	1
Number of socket outlets Type 3	0
Number of vehicle connectors CHAdeMO	0
Number of vehicle connectors Type 1	0
Number of vehicle connectors Type 1 CCS	0
Number of vehicle connectors Type 2	0
Number of vehicle connectors Type 2 CCS	0

**Main electrical features**

Nominal voltage	230/400 V
Frequency	50 Hz
Rated current	32 A

**Dimensions**

Depth of installed product	233 mm
Height of installed product	480 mm
Length	480 mm
Width of installed product	346 mm

**Power**

connected load	22 kW
Max. power per charging point	22 kW

**Power supply**

Number of phases for the power supply	3 phases
---------------------------------------	----------

**Materials**

RAL colour	RAL 7035 - Light grey
Material	plastic

Material group other

---

**Equipment**

With energy meter	No
With house connection box	No
Number of household socket outlets	1
Number of vehicle connectors GB AC	0
Number of vehicle connectors GB DC	0
With circuit breaker	No

---

**Standards**

European directive RoHS compliant

---

**Safety**

Protection index IP	IP54
REACH conform	No
Halogen free	No
Impact strength	IK10