



10112189

## Frame 1gang, R.1, p. white glossy

### Technical characteristics

#### Dimensions

|        |         |
|--------|---------|
| Depth  | 9.9 mm  |
| Height | 80.7 mm |
| Width  | 80.7 mm |

#### Capacity

|                   |   |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

#### Materials

|                           |                       |
|---------------------------|-----------------------|
| Colour of labelling       | 105,105,105           |
| Colour of design line     | polar white           |
| Colour                    | white                 |
| RAL colour                | RAL 9010 - Pure white |
| Material for printing     | ASA polar white       |
| Surface appearance        | glossy                |
| Type of surface treatment | untreated             |

#### Installation, mounting

|                   |  |
|-------------------|--|
| Installation mode | for vertical and horizontal mounting ; clamp fastening |
|-------------------|--|

#### Settings

|                   |          |
|-------------------|----------|
| Shading parameter | R1_biały |
| Laser parameter   | R1_weiß  |

#### Safety

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |
| Halogen free  | Yes |

#### Identification

|                  |            |
|------------------|------------|
| Main design line | Berker R.1 |
|------------------|------------|

#### Instructions

|                   |   |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|