



10112339

Frame 1gang, R.1, orange trans./p. white glossy, acrylic

Technical characteristics

Dimensions

| | |
|--------|---------|
| Depth | 9.9 mm |
| Height | 81.2 mm |
| Width | 81.2 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

Materials

| | |
|------------------------------|--------------------------------|
| Design lines special colours | orange transparent/polar white |
| Material / workmanship | acrylic |
| Surface appearance | glossy |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|-------------------|--|
| Installation mode | for vertical and horizontal mounting ; clamp fastening |
|-------------------|--|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |

Identification

| | |
|------------------|------------|
| Main design line | Berker R.1 |
|------------------|------------|

Instructions

| | |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
| Information text | Not suitable for water-protected, flush-mounted installation IP44. |