



10122189

Frame 2gang, R.1, p. white glossy

Technical characteristics

Dimensions

| | |
|--------|----------|
| Depth | 9.9 mm |
| Height | 151.7 mm |
| Width | 80.7 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 2 |
|-------------------|---|

Materials

| | |
|---------------------------|-----------------------|
| Colour of design line | polar white |
| Colour | polarwhite |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Material | thermoplastic |
| Material for printing | ASA polar white |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|-------------------|---|
| Installation mode | for vertical and horizontal mounting, clamp fastening |
|-------------------|---|

Settings

| | |
|-------------------|----------|
| Shading parameter | R1_biały |
| Laser parameter | R1_weiß |

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Identification

| | |
|------------------|------------|
| Main design line | Berker R.1 |
|------------------|------------|

Instructions

| | |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|