



10122289

### Frame 2gang, R.3, p. white glossy

#### Technical characteristics

##### Dimensions

Depth	9.9 mm
Height	151.75 mm
Width	80.75 mm

##### Capacity

Number of sockets	2
-------------------	---

##### Materials

Colour of labelling	105,105,105
Colour of design line	polar white
Colour	white
RAL colour	RAL 9010 - Pure white
Material for printing	ASA polar white
Surface appearance	glossy
Type of surface treatment	untreated

##### Installation, mounting

Installation mode	for vertical and horizontal mounting ; clamp fastening
-------------------	--

##### Settings

Shading parameter	R1_biały
Laser parameter	R1_weiß

##### Equipment

Type of configuration	Laserdruck
-----------------------	------------

##### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

##### Identification

Main design line	Berker R.3
------------------	------------

##### Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
-------------------	---