



10152289

### Frame 5gang, R.3, p. white glossy

#### Technical characteristics

##### Dimensions

|        |          |
|--------|----------|
| Depth  | 9.9 mm   |
| Height | 364.7 mm |
| Width  | 80.75 mm |

##### Capacity

|                   |   |
|-------------------|---|
| Number of sockets | 5 |
|-------------------|---|

##### Materials

|                           |                         |
|---------------------------|-------------------------|
| Colour of design line     | polar white             |
| Colour                    | polarwhite              |
| Colour                    | white                   |
| RAL colour                | RAL 9010 - Pure white   |
| Material                  | thermoplastic           |
| Material for printing     | ASA polar white         |
| Material / surface        | metal, aluminum profile |
| Type of surface treatment | untreated               |

##### Installation, mounting

|                   |                                                       |
|-------------------|-------------------------------------------------------|
| Installation mode | for vertical and horizontal mounting, clamp fastening |
|-------------------|-------------------------------------------------------|

##### Settings

|                   |          |
|-------------------|----------|
| Shading parameter | R1_biały |
| Laser parameter   | R1_weiß  |

##### Equipment

|                       |            |
|-----------------------|------------|
| Type of configuration | Laserdruck |
|-----------------------|------------|

##### Safety

|                     |      |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

##### Identification

|                  |            |
|------------------|------------|
| Main design line | Berker R.3 |
|------------------|------------|

##### Instructions

|                   |                                                                                                                                 |
|-------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---------------------------------------------------------------------------------------------------------------------------------|