



1061

Double pole socket outlet for floating output module inserts

Technical characteristics

Dimensions

Insertion depth	17.5 mm
-----------------	---------

Materials

Material	Plastic/metal
Surface appearance	other

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Conductor cross-section (rigid)	max. 6 mm ²
Connection pins	according to DIN 42801
Type of connection	with screw terminals

Use

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

Identification

Application, usage	Connecting systems and accessories
Main design line	Accessories
Secondary design line(s)	ACCESSORIES ; Berker Arsys ; Berker B.3 ; Berker B.7 ; Berker S.1 ; wg-up ip 44