



1061

Double pole socket outlet for floating output module inserts

Technical characteristics

Dimensions

Insertion depth 17.5 mm

Materials

Surface appearance other

Installation, mounting

Installation mode without spreader claws

Connection

Conductor cross-section (rigid) max. 6 mm²

Connection pins according to DIN 42801

Type of connection with screw terminals

Use

Differentiation characteristic 3 - Sales with screw terminals

Safety

REACH conform Yes

RoHS conform Yes

Identification

Application, usage Connecting systems and accessories

Main design line Accessories

Secondary design line(s) ACCESSORIES ; Berker Arsys ; Berker B.3 ; Berker B.7 ; Berker S.1 ; wg-up ip 44