



109200

Glass end frame, clear glossy

Technical characteristics

Dimensions

| | |
|--------|--------|
| Depth | 5.8 mm |
| Height | 77 mm |
| Width | 80 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

Materials

| | |
|---------------------------|-----------------|
| Colour of design line | clear |
| Colour | Natural colour |
| Material | glass |
| Surface appearance | glossy |
| Material / surface | toughened glass |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|-------------------|--|
| Installation mode | for combination mounting ; clamp fastening |
|-------------------|--|

Equipment

| | |
|----------|-------------------------------|
| Subplate | with polar white plastic base |
|----------|-------------------------------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Identification

| | |
|------------------|------------|
| Main design line | Serie Glas |
|------------------|------------|

Instructions

| | |
|------------------|---|
| Information text | Combinations are only to be installed in simple combi boxes. ; Special variant for hollow-wall mounting available on request. |
|------------------|---|