



109300

### Glass centre frame, clear glossy

#### Technical characteristics

##### Dimensions

|        |        |
|--------|--------|
| Depth  | 5.8 mm |
| Height | 77 mm  |
| Width  | 80 mm  |

##### Capacity

|                   |   |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

##### Materials

|                           |                 |
|---------------------------|-----------------|
| Colour of design line     | clear           |
| Surface appearance        | glossy          |
| Material / surface        | toughened glass |
| Type of surface treatment | untreated       |

##### Installation, mounting

|                   |  |
|-------------------|--|
| Installation mode | for combination mounting ; clamp fastening |
|-------------------|--|

##### Equipment

|          |                               |
|----------|-------------------------------|
| Subplate | with polar white plastic base |
|----------|-------------------------------|

##### Safety

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |

##### Identification

|                  |            |
|------------------|------------|
| Main design line | Serie Glas |
|------------------|------------|

##### Instructions

|                  |   |
|------------------|---|
| Information text | Combinations are only to be installed in simple combi boxes. ; Special variant for hollow-wall mounting available on request. |
|------------------|---|