



12033515

**Aerial soc., 2hole hinged cover surf.-mtd, single soc., W.1, light grey matt**

**Technical characteristics**

**Connectivity**

Connectors / jacks with IEC jacks (male/female)

Reception / transmission for terrestrial reception, for digital and analogue transmission

**Resistance**

Wave impedance 75  $\Omega$

**Cover, door**

Hinged covers with transparent hinged cover

**Connection**

Type of connection with screw terminals

**Cable**

Wire with one entry for 2 cables and one entry for cable and tube

**Standards**

General standards DIN EN 50083-2

**Safety**

Protection index IP IP55

REACH conform Yes

RoHS conform Yes

**Use conditions**

Operating temperature -40...30 °C

Storage/transport temperature -50...50 °C

**Identification**

Application, usage Communication technology

Main design line Berker W.1

**Instructions**

Information text Hinged cover springs made of stainless steel, pins of quick-release lock made of ZAMAK