



12033542

Aerial soc. insert 2hole hinged cover surf.-mtd, single soc., W.1, p.wh.m.plas.

Technical characteristics

Connectivity

Connectors / jacks	with IEC jacks (male/female)
Reception / transmission	for terrestrial reception, for digital and analogue transmission

Resistance

Wave impedance	75 Ω
----------------	-------------

Cover, door

Hinged covers	with transparent hinged cover
---------------	-------------------------------

Materials

Colour	polarwhite
--------	------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Standards

General standards	DIN EN 50083-2
-------------------	----------------

Safety

Protection index IP	IP55
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-40...30 °C
Storage/transport temperature	-50...50 °C

Identification

Application, usage	Communication technology
Main design line	Berker W.1

Instructions

Information text	Hinged cover springs made of stainless steel, pins of quick-release lock made of ZAMAK
------------------	--