



12033562

Aerial soc. insert 3hole hinged cover surf.-mtd, single soc., W.1, p.wh.m.plas.

Technical characteristics

Connectivity

Connectors / jacks	with 'F' connector ; with IEC jacks (male/female)
Reception / transmission	for terrestrial and SAT reception ; for digital and analogue transmission

Frequency

Broadband technology	4...2400 MHz
----------------------	--------------

Resistance

Wave impedance	75 Ω
----------------	-------------

Attenuation

Tap loss at 2150 MHz	2 dB
Tap loss at 860 MHz	5 dB

Cover, door

Hinged covers	with transparent hinged cover
---------------	-------------------------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Cable

Wire	with one entry for 2 cables and one entry for cable and tube
------	--

Standards

General standards	DIN EN 50083-2
-------------------	----------------

Safety

REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-40...30 °C
Storage/transport temperature	-50...50 °C

Identification

Application, usage	Communication technology
Main design line	Berker W.1

Instructions

Information text	Hinged cover springs made of stainless steel, pins of quick-release lock made of ZAMAK
------------------	--