



13293502

Frame 2gang horizontal for flush-mounted installation, with sealing, W.1, p-w

Technical characteristics

Dimensions

Depth	38 mm
Height	83 mm
Width	154 mm

Capacity

Number of sockets	2
-------------------	---

Materials

Colour of design line	polar white
Surface appearance	glossy
Type of surface treatment	untreated

Installation, mounting

Installation mode	for flush-mounted and hollow-wall mounting ; with mounting adapter and sealing ; for horizontal mounting
-------------------	--

Use

Differentiation characteristic 2 - Sales	with sealing
--	--------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Application, usage	Flush-mounted wet-room installation
Main design line	Berker W.1

Instructions

Special note text	The degree of protection IP55 will only be reached if mounted with a modular flush-mounted insert of the Berker W.1 product line
-------------------	--