



13293515

**Frame 2gang vertical for flush-mounted installation, with sealing W.1 light grey**

**Technical characteristics**

**Dimensions**

Depth	9.9 mm
Height	158 mm
Width	80.5 mm

**Capacity**

Number of sockets	2
-------------------	---

**Materials**

Colour of design line	light grey
Surface appearance	glossy
Type of surface treatment	untreated

**Installation, mounting**

Installation mode	for flush-mounted and hollow-wall mounting ; with mounting adapter and sealing ; for vertical mounting
-------------------	--

**Use**

Differentiation characteristic 2 - Sales	with sealing
--	--------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Use conditions**

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

**Identification**

Application, usage	Flush-mounted wet-room installation
Main design line	Berker W.1

**Instructions**

Special note text	The degree of protection IP55 will only be reached if mounted with a modular flush-mounted insert of the Berker W.1 product line
-------------------	--