



13293515

Frame 2gang vertical for flush-mounted installation, with sealing W.1 light grey

Technical characteristics

Dimensions

Depth	9.9 mm
Height	158 mm
Width	80.5 mm

Capacity

Number of sockets	2
-------------------	---

Materials

Colour of design line	light grey
Colour	light grey
Material	thermoplastic
Type of surface treatment	untreated

Installation, mounting

Installation mode	for flush-mounted and hollow-wall mounting, with mounting adapter and sealing, for vertical mounting
-------------------	--

Use

Differentiation characteristic 2 - Sales	with sealing
--	--------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Application, usage	Flush-mounted wet-room installation
Main design line	Berker W.1

Instructions

Special note text	The degree of protection IP55 will only be reached if mounted with a modular flush-mounted insert of the Berker W.1 product line
-------------------	--