



13303502

**Frame 3gang hor. for flush-mtd inst., sealing, W.1, p. white, matt, plastic**

**Technical characteristics**

**Dimensions**

Depth	38 mm
Height	224 mm
Width	83 mm

**Capacity**

Number of sockets	3
-------------------	---

**Materials**

Colour of design line	polar white
Colour	white
RAL colour	RAL 9010 - Pure white
Surface appearance	matt
Type of surface treatment	untreated

**Installation, mounting**

Installation mode	for flush-mounted and hollow-wall mounting ; with mounting adapter and sealing ; for horizontal mounting ; with clamp/screw fastening
-------------------	---

**Use**

Differentiation characteristic 2 - Sales	with sealing
--	--------------

**Use conditions**

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

**Identification**

Application, usage	Flush-mounted wet-room installation
Main design line	Berker W.1

**Instructions**

Special note text	The degree of protection IP55 will only be reached if mounted with a modular flush-mounted insert of the Berker W.1 product line
-------------------	--