



13303502

Frame 3gang hor. for flush-mtd inst., sealing, W.1, p. white, matt, plastic

Technical characteristics

Dimensions

Depth	38 mm
Height	224 mm
Width	83 mm

Capacity

Number of sockets	3
-------------------	---

Materials

Colour of design line	polar white
Colour	white
RAL colour	RAL 9010 - Pure white
Surface appearance	matt
Type of surface treatment	untreated

Installation, mounting

Installation mode	for flush-mounted and hollow-wall mounting ; with mounting adapter and sealing ; for horizontal mounting ; with clamp/screw fastening
-------------------	---

Use

Differentiation characteristic 2 - Sales	with sealing
--	--------------

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Application, usage	Flush-mounted wet-room installation
Main design line	Berker W.1

Instructions

Special note text	The degree of protection IP55 will only be reached if mounted with a modular flush-mounted insert of the Berker W.1 product line
-------------------	--