



13383513

**Frame 1gang, can be illuminated 230 V, for housing surface-mtd, W.1, blue**

#### Technical characteristics

##### Main electrical features

Rated current	2.5 mA
---------------	--------

##### Dimensions

Depth	23 mm
Height	83 mm
Width	83 mm

##### Endurance

Service life of the LED	30000 h
-------------------------	---------

##### Capacity

Number of sockets	1
-------------------	---

##### Materials

Colour	light grey
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	thermoplastic
Surface appearance	matt
Type of surface treatment	untreated

##### Lighting control

Light colour	blue
--------------	------

##### Installation, mounting

Installation mode	with clamp/screw fastening
-------------------	----------------------------

##### Equipment

Lighting	for lighting and monitoring circuit
----------	-------------------------------------

##### Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

##### Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

##### Identification

Instructions

Information text

Caution! Mount only in conjunction with a surface-mounted housing.