



13383513

Frame 1gang, can be illuminated 230 V, for housing surface-mtd, W.1, blue

#### Technical characteristics

##### Main electrical features

Rated current	2.5 mA
---------------	--------

##### Dimensions

Depth	23 mm
-------	-------

Height	83 mm
--------	-------

Width	83 mm
-------	-------

##### Endurance

Service life of the LED	30000 h
-------------------------	---------

##### Capacity

Number of sockets	1
-------------------	---

##### Materials

Colour	light grey
--------	------------

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Surface appearance	matt
--------------------	------

Type of surface treatment	untreated
---------------------------	-----------

##### Lighting control

Light colour	blue
--------------	------

##### Installation, mounting

Installation mode	with clamp/screw fastening
-------------------	----------------------------

##### Equipment

Lighting	for lighting and monitoring circuit
----------	-------------------------------------

##### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

##### Use conditions

Operating temperature	-15...30 °C
-----------------------	-------------

Storage/transport temperature	-50...50 °C
-------------------------------	-------------

##### Identification

Main design line	Berker W.1
------------------	------------

##### Instructions

